

Unwrapped
FAST / 134°C

9 min

Wrapped
Class B / 134°C


18 min

Wrapped
Class B / 121°C

30 min

Wrapped / PRION
Class B / 134°C

43 min




x16

**Enbio PRO Autoclave
Technical Data**



Class B
Vacuum
Pouches+
drying

Capacity



x16

Bottom
tray

Top tray
(for small
instruments)
20×18×2 cm



Load space
29×19×8 cm

Max. packages amount (circa) **16**
Max. recommended batch weight **1,0 kg**
Process chamber volume **5,3 l**




Power supply

Enbio PRO works with any
typical electrical outlet.



Data archiving

All process data are
automatically written
to a USB disk.



Water supply

Enbio uses distilled water
from external tank. With
Enbio Magic Filter, water
can be recycled.



Process reports

Enbio Data Viewer (included)
allows generating and printing
detailed process reports from
the data on USB.

Dimensions

56 cm



27 cm



20 cm

Pressure & temperature

Working pressure **2,1 Bar**
Max. pressure **2,3 Bar**
Max. process temperature **137°C**

Electrical

Power supply **230V/50Hz**
Installed power **3250 W**
Max. power consumption **15 A**

Misc

Ingress protection **IP20**
Data archiving **USB**
Water conductivity* **< 15 µS/cm**

* - demineralized water only



Enbio Group AG
Eichengasse 3, 4702 Oensingen
Switzerland

enbio.com

Unwrapped
FAST / 134°C


7 min

Wrapped
Class B / 134°C

15 min

Wrapped
Class B / 121°C

30 min




x8

**Enbio^S Autoclave
Technical Data**




Class B
Vacuum
Pouches+
drying

Capacity



x8



Load space
28×18×3,5 cm

Max. packages amount (circa) **8**
Max. recommended batch weight **0,5 kg**
Process chamber volume **2,7 l**




Power supply

Enbio PRO works with any typical electrical outlet.



Data archiving

All process data are automatically written to a USB disk.



Water supply

Enbio uses distilled water from external tank. With Enbio Magic Filter, water can be recycled.



Process reports

Enbio Data Viewer (included) allows generating and printing detailed process reports from the data on USB.

Dimensions



Pressure & temperature

Working pressure **2,1 Bar**
Max. pressure **2,3 Bar**
Max. process temperature **137°C**

Electrical

Power supply **230V/50Hz**
Installed power **2250 W**
Max. power consumption **15 A**

Misc

Ingress protection **IP20**
Data archiving **USB**
Water conductivity* **< 15 µS/cm**

* - demineralized water only



Enbio Group AG
Eichengasse 3, 4702 Oensingen
Switzerland

enbio.com